

# 620Di and 620DiN with 620LG pumphead

620 series dispensing pumps

**Flexicon**  
Liquid Filling

## Features and benefits

- Keypad entry of flow from 0.001 L/min to 18 L/min
- Dispenses 500 ml to within  $\pm 0.5\%$
- Stores up to 50 dispensing programs
- Up to 4 bar pressure
- 2650:1 control ratio (0.1 to 265 rpm speed range)
- Digital speed adjustment with choice of 0.1 rpm, 0.5 rpm, 1 rpm, 2 rpm, 5 rpm and 10 rpm step changes
- Maintenance-free brushless DC motor
- Smooth easy-to-clean enclosure free from bug traps



## 620Di and 620DiN with 620LG pumphead performance

Flow ranges (L/min) (over 0.1 to 265rpm speed range)	Y element tubing (single channel)			Continuous tubing (flow per channel - max of 2 channels)		
Tubing material	8.0mm	12.0mm	16.0mm	8.0mm	12.0mm	16.0mm
Pumpsil silicone	0.002-4.6	0.003-8.5	0.005-11.5	0.001-2.3	0.002-4.3	0.003-5.8
Marprene, Bioprene	0.002-4.6	0.003-8.5	0.005-11.5	0.001-2.3	0.002-4.3	0.003-5.8
STA-PURE PCS	0.002-5.2	0.003-9.0	0.005-12.4	0.001-2.6	0.002-4.5	0.003-6.2
620LG dose sizes (STA-PURE PCS®, STA-PURE PFL®)						
Tube bore	8.0mm		12.0mm	16.0mm		
Minimum possible dose	10ml		17ml	23ml		
Minimum recommended	99ml		167ml	234ml		


## Technical specifications

	620Di and 620DiN with 620LG pumphead
Filling volume range	Up to 500ml in 2.4s ml
Accuracy	$\pm 0.5\%$
Ingress Protection	IP31, IP66, NEMA 2, NEMA 4X
Operating temperature	5 °C to 40 °C (40 °F to 104 °F)
Speed control ratio	2650:1
Humidity	(Condensing) 10 to 100 % RH, (Non-condensing) 80 % up to 31 °C (88 °F) decreasing linearly to 50 % at 40 °C (104 °F)
Noise	<70dB(A) at 1m
Standards	CE, cETLus
Power supply	100 V to 120 V, 200 V to 240 V, 50/60 Hz, Single-phase
Weight	24.3 - 25.2 kg (53.6 - 55.6 lbs)
Accessories	Footswitch, handswitch, RS232 cable, batch records cable
Compatible tubing size	12.0 mm ID, 16.0 mm ID, 4.0 mm wall thickness, 8.0 mm ID

## Materials of construction

	620Di and 620DiN with 620LG pumphead
Bearings	Carbon steel
Casework	Pressure die-cast aluminium LM24
Keypad/HMI	Polyester
Pumphead roller assembly	Stainless steel

## 620Di and 620DiN with 620LG pumphead dimensions



## Control options

	620Di	620DiN
Enclosure - ingress protection rating	IP31	IP66
<b>Manual control</b>		
Digital speed control with simple calibration to display flow	✓	✓
Choice of flow rate display; metric or imperial units	✓	✓
Numeric keypad for entry of speed, flow or PIN code	✓	✓
<b>Remote control</b>		
Run/stop, direction change, auto/manual mode, leak detector input (via contact closure or 5V TTL to 24V industrial logic)	✓	✓
Remote operation of dosing (foot/handswitch or logic input)	✓	✓
Four programmable digital status outputs through 5V TTL to 24V industrial logic		✓
Analogue speed feedback		
Tachometer output; 0-1478Hz	✓	✓
<b>Digital communication</b>		
Digital network serial control RS232 RS485	RS232	RS485
<b>Specialist dispensing functionality</b>		
Drip control feature (momentary direction reverse at end of dose)	✓	✓
Ramp control to improve accuracy and avoid splashing or frothing	✓	✓
Export of batch records to PC or printer for cGMP requirements RS232	RS232	
Dual operator/supervisor PIN code protection of pump settings	✓	✓

## Product codes

Product codes					
620LG pumphead		Accessories			
Pumphead only	063.4623.000	Footswitch	Handswitch	RS232 cable	Batch records cable
<b>IP31/NEMA 2 wipe-down pumps</b>	<b>IP31</b>	<b>IP31</b>	<b>IP31</b>	<b>IP31</b>	
620Di/LG	060.4171.5G0*	059.3002.000	059.3022.000	059.3121.000	059.3125.000
* Replace last zero with A, E, U, K, R, D, Z or C for 2.8m American, European, United Kingdom, Australian, Argentinian, South African, Chinese or Swiss mains plug					
<b>IP66/NEMA 4X wash-down pumps</b>	<b>IP55</b>			<b>IP65</b>	
620DiN/LG	060.417N.5G0**	069.5231.000	n/a	n/a	n/a
** Replace last zero with A, C, K, R or Z plug type					
Y element tubing					
Bore size (4.0mm wall thickness)	8.0mm	12.0mm	16.0mm	8.0mm	12.0mm
Tubing material					16.0mm
Pumpsil silicone	913.AE80.K40	913.A12E.K40	913.A16E.040	913.A080.040	913.A120.040
Marprene	902.E080.K40	902.E120.K40	902.E160.040	902.0080.040	902.A120.040
Bioprene	933.E080.K40	933.E120.K40	933.E160.040	933.0080.040	933.A120.040
STA-PURE PCS	961.E080.K40	961.E120.K40	961.E160.040		933.0160.040
			Clamp set for continuous tube		069.4001.000
NB: 4 bar pressure capability with STA-PURE PCS elements					

Disclaimer: The information in this document is believed to be correct, but Watson-Marlow Flexicon A/S accepts no liability for any errors it contains, and reserves the right to alter specifications without notice. **WARNING:** These products are not designed for use in, and should not be used for, patient-connected applications. WMArchitect and Accusil are registered trademarks.

wmfts.com/global  
14 July 2025

